



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L5.5FB11E12930C 5.5W Led B11 Straight Tip 30K CNDL Base Clear 500L *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | L5.5FB11E12930C |
| Manufacturer | Keystone Technologies |
| Description | Straight Tip Chandelier Filament Bulb, 60W Equivalent, B11 Shape, E12 Candalbra Base, 3000K, 90 Cri , Clear |
| Weight per unit | 0.1100 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|------|
| Ballast Type | N/A |
| Circuit Type | N/A |
| Input Voltage | 120V |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Voltage | N/A |
| Warranty | 3 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|---------------|-----|
| Base Type | E12 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Clear Glass |
| Description | 5.5W LED B11 STRAIGHT TIP 30K CNDL BASE CLEAR 500L |
| extra long description | Key KT-LED5.5FB11-E12-930-C 60W Equ |
| Long Description | Straight Tip Chandelier Filament bulb, 60W Equivalent, B11 shape, E12 Candalbra base, 3000K, 90 CRI , Clear |
| Product Type | 60W Equiv., 5.5W, 500 Lumen, B11, E12, =90 Cri, Dimmable 27K |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Keystone |
| GTIN | 00843654123752 |
| Manufacturers Part Number | KT-LED5.5FB11-E12-930-C |
| UPC | 843654123752 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED DECORATIVE C, CA, F, G SHAPE LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 24 |
| Weight Per each | 0.11 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Energy Star Y