



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L530R Turnlok Recp SGL 3W 30A 125V

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | L530R |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlock Single Receptacle, 30 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back Wire Connection, Receptacle, 1.62 In Length, 1.28 In Width, 3.28 In Height, Nylon Material, Black, Impact Resistant, 0.2200 LB |
| Weight per unit | 0.2228 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|-------------|
| amperage rating | 30 |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | TURNLOK RECP SGL 3W 30A 125V |
| extra long description | P&S L530R TURNLOK RECEPT SINGLE 3WI |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007253054 |
| Manufacturers Part Number | L530R |
| UPC | 785007253054 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Turnlock Single Receptacle |

Trade Size

| | |
|----------|------|
| Amperage | 30.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.2228 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

Receptacle
FEDSPEC, CULUS, UL 498