



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L838 8AWG Cu Com Lug

*Nsi Industries*

Catalog Number	L838
Manufacturer	Nsi Industries
Description	1 Hole Long Barrel Copper Compression Lug 8 Awg - 3/8" Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Low Contact Resistance. Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed and to Cable Manufacturer Instructions. Temperature Rating 90 Degrees C. .
Weight per unit	2.2 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

Cable Size	# 8 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Red
Finish	Tin Plated

### Dimensions and Weight

Size	L=1.52 - W=.420 - OD=.295 - ID=.205
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	8AWG CU COM LUG
extra long description	NSI L838 CU CMP Lug Long 8 AWG 3/8
Features	1 Hole Long Barrel Copper Compression Lug 8 AWG - 3/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Long Description	1 Hole Long Barrel Copper Compression Lug 8 AWG - 3/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Product Type	Cu CMP Lug Long 8 Awg 3/8 Bolt Size
Special Features	# 8 AWG (STR) - 3/8 Mounting Hole

## Manufacturer Information

Brand	NSi
GTIN	00662381336293
Manufacturers Part Number	L838
UPC	662381336293

## Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Long Barrel - One Hole

## Packaging

Carton	1
Weight Per each	2.2

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)