



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LC125DCG 1.25" Cond Body C/G

Appleton/Oz Gedney

Catalog Number	LC125DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Fi Nish, Gasket: Neoprene, Ul Standard: 514A, Trade Size: 1-1/4", L
Weight per unit	2.0 (lbs/each)
Product Category	Alum

Features

Material	Die Cast Aluminum
----------	-------------------

Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

Dimensions and Weight

Height	2.97
Hub Size	1-1/2
Length	8.45
Width	2.49

Descriptions

Description	1.25" COND BODY C/G
extra long description	EGS LC125DCG 1-1/4 THD ALUM LC BDY
Long Description	EMT Conduit Bodies, Aluminum Threaded for Rigid Conduit and IMC, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural fi nish, Gasket: neoprene, UL Standard: 514A, Trade Size: 1-1/4", L
Product Type	1-1/4 THD Alum LC Bdy CVR GSKT
Special Features	1-1/4 IN Trade Size, Type LC Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #2 AWG, Volume 33.40IN ³ , For Use With Rigid and IMC Conduit, Furnished With Stamped Aluminum Cover and Neoprene Gasket

Manufacturer Information

Brand	Appleton
GTIN	00687855000623
Manufacturers Part Number	LC125DCG
UPC	687855000623



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body

Packaging

Carton	20
Weight Per each	2

Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A