



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBH30 1" LBH Conduit Body

Crouse-Hinds

Catalog Number	LBH30
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet LBH Conduit Outlet Body With Cover, Feraloy Iron Alloy, 1"
Weight per unit	8.6 (lbs/each)
Product Category	Bodies & Covers

Features

connection	Threaded
dimensions	7.8800 IN X 4.0000 IN X 7.0000 IN

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Height	5-1/4
Hub Size	1 in
Width	4

Descriptions

Description	1" LBH CONDUIT BODY
extra long description	CRS-H LBH30 1 CNDT OUTLET BODY
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet LBH conduit outlet body with cover, Feraloy iron alloy, 1"
Product Type	1 CNDT Outlet Body
Special Features	With Cover

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274519258
Manufacturers Part Number	LBH30
UPC	782274519258



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Conduit outlet body with cover

Packaging

Carton	1
Weight Per each	8.6499

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2