



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCAS4038X 1HOLE Lug Panduit Corporation

| | |
|------------------|--|
| Catalog Number | LCAS4038X |
| Manufacturer | Panduit Corporation |
| Description | One-Hole, Short Barrel With Window Lug, 4/0 Awg Wire, 3/8 Stud Hole. |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|-------------------|
| Material | Tin-Plated Copper |
| Number of Holes | 1 |
| Stud Size | 42.95 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Purple |
|-------|--------|

Dimensions and Weight

| | |
|------|--------------|
| Size | 4/0 AWG Code |
|------|--------------|

Descriptions

| | |
|------------------------|---|
| Description | 1HOLE LUG |
| extra long description | PAN LCAS4/0-38-X CuLug,4/0AWG,Short |
| Long Description | One-hole, short barrel with window lug, 4/0 AWG wire, 3/8 stud hole. |
| Product Type | Culug, 4/0AWG, Short, 3/8studpkg10 |
| Special Features | Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Panduit Corporation |
| GTIN | 00074983225118 |
| Manufacturers Part Number | LCAS4/0-38-X |
| UPC | 074983225118 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Tin-Plated Copper Compression Connectors - Lugs |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|----|
| Carton | 10 |
| Package | 1 |
| Weight Per each | 1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|----------|---|
| Mounting | 1 |
| standard | C22.2 No. 65-13, 486A-486B File #E52164 |