



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCCF4038DX Two-Hole, Long Flared Bar Panduit Corporation

| | |
|------------------|--|
| Catalog Number | LCCF4038DX |
| Manufacturer | Panduit Corporation |
| Description | Two-Hole, Long Flared Barrel, 4/0 Awg Wire, 3/8 Stud Hole, 1 Hole Spacing. |
| Weight per unit | 2.1 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|-------------------|
| Material | Tin-Plated Copper |
| Number of Holes | 2 |
| Stud Size | 3/8 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Yellow |
|-------|--------|

Dimensions and Weight

| | |
|------|-------------------------------|
| Size | 4/0 AWG Class K and M and DLO |
|------|-------------------------------|

Descriptions

| | |
|------------------------|---|
| Description | TWO-HOLE, LONG FLARED BAR |
| extra long description | PAN LCCF4/0-38D-X Pan-Lug™ LCCF4/0- |
| Long Description | TWO-HOLE, LONG FLARED BARREL, 4/0 AWG WIRE, 3/8 STUD HOLE, 1 HOLE SPACING. |
| Product Type | Pan-Lug™ LCCF4/0-38D-X Comp. Lug, 4/0, Flare, Tin PLT Copper |
| Special Features | Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 V |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983753178 |
| Manufacturers Part Number | LCCF4/0-38D-X |
| UPC | 074983753178 |

Taxonomies, Classifications, and Categories

| | |
|------|-----------------|
| Type | Compression Lug |
|------|-----------------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 2.142 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

1-11/16

CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File
#E52164, NEBS Level 3