



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED12T848G840S 12W Led T8 48" 40K BLSTD

Keystone Technologies

| | |
|------------------|--|
| Catalog Number | LED12T848G840S |
| Manufacturer | Keystone Technologies |
| Description | 12W Led T8 Lamp, 4FT, 4000K. Smartdrive. Glass Construction. Designed For Use With Instant Start Ballasts Only. |
| Weight per unit | 0.6600 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|-------------------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | Ballast Dependent |
| ip rating | N/A |
| lumens | 1800 |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 12 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | N/A |
| Description | 12W LED T8 48" 40K BLSTD |
| extra long description | Key KT-LED12T8-48G-840-S /G2-CP 12W |
| Long Description | 12W LED T8 LAMP, 4FT, 4000K. SMARTDRIVE. GLASS CONSTRUCTION. DESIGNED FOR USE WITH INSTANT START BALLASTS ONLY. |
| Product Type | 12W, 1800 Lumen, 4', 220' Beam Angle, Ballast Compatible, DL |

Manufacturer Information

| | |
|---------------------------|-----------------------------|
| Brand | Keystone |
| GTIN | 00890949016718 |
| Manufacturers Part Number | KT-LED12T8-48G-840-S /G2-CP |
| UPC | 890949016718 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|--------|----|
| Carton | 25 |
|--------|----|

| | |
|-----------------|------|
| Weight Per each | 0.66 |
|-----------------|------|

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | Y |
|-------------|---|