



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED25.5T5H048GC8 25W Led T5HO 48" 50K Ballast Compatible Glass

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | LED25.5T5H048GC8 |
| Manufacturer | Keystone Technologies |
| Description | 25.5W Led T5HO Tube, Shatter-Proof Coated Glass, Ballast Compatible, 4, 5000K, Smartdrive |
| Weight per unit | 0.4800 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|-------------------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | Ballast Dependent |
| ip rating | N/A |
| lumens | 3300 |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 25.5 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G5 |
| color rendering index (cri) | >80 Deg |
| color temperature | 5000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Shatterproof Glass |
| Description | 25W LED T5HO 48" 50K BALLAST COMPATIBLE GLASS |
| extra long description | Key KT-LED25.5T5HO-48GC-850-S-CP 25 |
| Long Description | 25.5W LED T5HO TUBE, SHATTER-PROOF COATED GLASS, BALLAST COMPATIBLE, 4, 5000K, SMARTDRIVE |
| Product Type | 25W, 3200 Lumen, 4', 240' Beam Angle, Ballast Compatible, DL |

Manufacturer Information

| | |
|---------------------------|------------------------------|
| Brand | Keystone |
| GTIN | 00890949013137 |
| Manufacturers Part Number | KT-LED25.5T5HO-48GC-850-S-CP |
| UPC | 890949013137 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|--------|---|
| Carton | 1 |
|--------|---|

| | |
|-----------------|------|
| Weight Per each | 0.48 |
|-----------------|------|

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|