



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED15T8U6GC840S 15W Led T8 Ubend 40K Coated Type A 2000LM

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | LED15T8U6GC840S |
| Manufacturer | Keystone Technologies |
| Description | 15W Led T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 6" U-Bend, 4000K, 12 PCS Carton, Carton Pack |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|-------------------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | Ballast Dependent |
| ip rating | N/A |
| lumens | 2200 |
| Nominal Length | 6 in U-Bend |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 15 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Shatterproof Glass |
| Description | 15W LED T8 UBEND 40K COATED TYPE A 2000LM |
| extra long description | Key KT-LED15T8-U6GC-840-S-CP 15W, 2 |
| Long Description | 15W LED T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 6" U-Bend, 4000K, 12 pcs Carton, Carton Pack |
| Product Type | 15W, 2000 Lumen, 4', 240' Beam Angle, Ballast Compatible, DL |

Manufacturer Information

| | |
|---------------------------|--------------------------|
| Brand | Keystone |
| GTIN | 00890949013410 |
| Manufacturers Part Number | KT-LED15T8-U6GC-840-S-CP |
| UPC | 890949013410 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|--------|----|
| Carton | 12 |
|--------|----|

| | |
|-----------------|------|
| Weight Per each | 1.03 |
|-----------------|------|

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|