



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED43T8H096G840D *Delisted* 43W Led T8HO 96" 4K 5500LDBL CNT Line V *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | LED43T8H096G840D |
| Manufacturer | Keystone Technologies |
| Description | 43W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 4000K, 120-277V Input, Internal Driver, Direct Drive |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 5500 |
| Nominal Length | 96 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 43 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | R17D |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | N/A |
| Description | *DELISTED* 43W LED T8HO 96" 4K 5500LDBL CNT LINE V |
| extra long description | Key KT-LED43T8HO-96G-840-D-CP 43W, |
| Long Description | 43W LED T8 LAMP, 8 LONG, GLASS CONSTRUCTION, R17D HO BASE, 4000K, 120-277V INPUT, INTERNAL DRIVER, DIRECT DRIVE |
| Product Type | 43W, 5550 Lumens, 8' 220' Beam Angle, Ballast Bypass, Rec. D |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|---------------------------|
| Brand | Keystone |
| GTIN | 00890949019269 |
| Manufacturers Part Number | KT-LED43T8HO-96G-840-D-CP |
| UPC | 890949019269 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Weight Per each | 1.32 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | Y |
|-------------|---|