



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED43T8H096G840D *Delisted* 43W Led T8HO 96" 4K 5500LDBL CNT Line V *Keystone Technologies*

Catalog Number	LED43T8H096G840D
Manufacturer	Keystone Technologies
Description	43W Led T8 Lamp, 8 Long, Glass Construction, R17D Ho Base, 4000K, 120-277V Input, Internal Driver, Direct Drive
Weight per unit	1.3 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5500
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	43
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	N/A
Description	*DELISTED* 43W LED T8HO 96" 4K 5500LDBL CNT LINE V
extra long description	Key KT-LED43T8HO-96G-840-D-CP 43W,
Long Description	43W LED T8 LAMP, 8 LONG, GLASS CONSTRUCTION, R17D HO BASE, 4000K, 120-277V INPUT, INTERNAL DRIVER, DIRECT DRIVE
Product Type	43W, 5550 Lumens, 8' 220' Beam Angle, Ballast Bypass, Rec. D



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00890949019269
Manufacturers Part Number	KT-LED43T8HO-96G-840-D-CP
UPC	890949019269

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	10
Weight Per each	1.32

Uses, Certifications, and Standards

Energy Star	Y
-------------	---