



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED36T896P840D 36W Led T8 96" 40K Line Voltage 3800LM Plastic

*Keystone Technologies*

Catalog Number	LED36T896P840D
Manufacturer	Keystone Technologies
Description	36W Led T8 Lamp, 8 Long, Single Pin Base, 4000K. 120-277V Input, Internal Driver. 20 PCS Carton, Individual Protective Sleeves. Direct Drive
Weight per unit	2.7 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	4000
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	36
Wire Type	N/A

### Material, Color, and Finish

Base Type	Fa8
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	N/A
Description	36W LED T8 96" 40K LINE VOLTAGE 3800LM
extra long description	Key KT-LED36T8-96P-840-D-DP 36W, 40
Long Description	36W LED T8 Lamp, 8 long, Single Pin Base, 4000K. 120-277V Input, Internal Driver. 20 pcs carton, Individual Protective Sleeves. Direct Drive
Product Type	36W, 4000 Lumens, 8', 120' Beam Angle, Ballast Bypass, Singl



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00890949011751
Manufacturers Part Number	KT-LED36T8-96P-840-D-DP
UPC	890949011751

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	20
Weight Per each	2.7

## Uses, Certifications, and Standards

Energy Star	N
-------------	---