



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED43T896G840D \*Delisted\* 43W Led T8 96" 40K Line VLT GLS SNGL Pin *Keystone Technologies*

Catalog Number	LED43T896G840D
Manufacturer	Keystone Technologies
Description	43W Led T8 Lamp, 8 Long, Glass Construction, Single Pin Base, 4000K, 120-277V Input, Internal Driver, Direct Drive
Weight per unit	1.4 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5500
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	43
Wire Type	N/A

### Material, Color, and Finish

Base Type	Fa8
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	N/A
Description	*DELISTED* 43W LED T8 96" 40K LINE VLT GLS SNGL PIN
extra long description	Key KT-LED43T8-96G-840-D-CP 43W, 55
Long Description	43W LED T8 LAMP, 8 LONG, GLASS CONSTRUCTION, SINGLE PIN BASE, 4000K, 120-277V INPUT, INTERNAL DRIVER, DIRECT DRIVE
Product Type	43W, 5500 Lumens, 8' 220' Beam Angle, Ballast Bypass, Single



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00890949019245
Manufacturers Part Number	KT-LED43T8-96G-840-D-CP
UPC	890949019245

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	10
Weight Per each	1.4

## Uses, Certifications, and Standards

Energy Star	Y
-------------	---