



GE
Lighting

69921 - GE LED MR16 Gen 2

LED7DMR16D830/35

Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Base Description	2-Pin
Base Type	Pin/Plug-In
Lamp Type	LED-MR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	GU5.3
Bulb Shape	MR16

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	1100 cd
Lumens per Watt (Efficacy)	56 lm
Nominal Initial Lumen per Watt	56
Rated Beam Spread	35 deg
Initial Lumens-nominal	390 lm
Color Rendering Index-CRI	83
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	69921
Description	LED7DMR16D830/35
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168699211
Standard Package GTIN	00043168699211
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168699211
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	12 V
Rated power (Watts)	7 W

CAUTIONS & WARNINGS

Warning

Risk of Electric Shock

Turn power off before inspection

installation or removal. Do not use where directly exposed to water. Not for use totally enclosed luminaires. For use with only approved Class 2 transformers/drivers.

Caution

null

Do not open - no user serviceable parts inside. Not intended for use with emergency exit fixtures or emergency exit lights.



GE
Lighting

69921 - GE LED MR16 Gen 2

LED7DMR16D830/35

Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Base Description	2-Pin
Base Type	Pin/Plug-In
Lamp Type	LED-MR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	GU5.3
Bulb Shape	MR16

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	1100 cd
Lumens per Watt (Efficacy)	56 lm
Nominal Initial Lumen per Watt	56
Rated Beam Spread	35 deg
Initial Lumens-nominal	390 lm
Color Rendering Index-CRI	83
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	69921
Description	LED7DMR16D830/35
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168699211
Standard Package GTIN	00043168699211
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168699211
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	12 V
Rated power (Watts)	7 W

CAUTIONS & WARNINGS

Warning

Risk of Electric Shock

Turn power off before inspection

installation or removal. Do not use where directly exposed to water. Not for use totally enclosed luminaires. For use with only approved Class 2 transformers/drivers.

Caution

null

Do not open - no user serviceable parts inside. Not intended for use with emergency exit fixtures or emergency exit lights.