



A simple upgrade to your existing high bay fixtures that can be done today!



## HIGH BAY RETROFITS

Ideal for use in:

- Large retail spaces
- Industrial spaces
- Auditoriums
- Gymnasiums
- Warehouses
- Factories

### Retrofits into most popular high bay fixtures



**100W**  
**LED-8036M**

Replaces up to  
250W



**140W**  
**LED-8030M\***

Replaces up to  
400W



**140W**  
**LED-8032M\***

Replaces up to  
400W

**Aims light upward,  
sideways, and down**

**Total downlight  
for ultra-high ceilings**

Ask about our metal halide ballast compatible models

\* Design Patent  
D723,194

\* Design Patent  
29/519,210

DESCRIPTION			LUMENS	POWER USED	REPLACES	BASE	CCT			DIMENSIONS
<b>LED-8036M 100W</b> HIGH BAY LIGHTING	LED-8036M40-A	LED-8036M40-A (120V) LED-8036M40C-A (347V)	Up to 10902	100W	250W	EX39	4000K	✓	✓	7.6" x 7.9"
	LED-8036M57-A	LED-8036M57-A (120V) LED-8036M57C-A (347V)	Up to 11015	100W	250W	EX39	5700K	✓	✓	7.6" x 7.9"
<b>LED-8030M 140W</b> HIGH BAY LIGHTING	LED-8030M40-A	LED-8030M40-A (120V) LED-8030M40C-A (347V)	Up to 15763	140W	400W	EX39	4000K	✓	✓	9.2" x 9.1"
	LED-8030M57A	LED-8030M57-A (120V) LED-8030M57C-A (347V)	Up to 15966	140W	400W	EX39	5700K	✓	✓	9.2" x 9.1"
<b>LED-8032M 140W</b> HIGH BAY LIGHTING	LED-8032M40-A	LED-8032M40-A (120V) LED-8032M40C-A (347V)	Up to 16668	140W	400W	EX39	4000K	✓	✓	9.4" x 9.1"
	LED-8032M57-A	LED-8032M57-A (120V) LED-8032M57C-A (347V)	Up to 16923	140W	400W	EX39	5700K	✓	✓	9.4" x 9.1"
<b>LED-8034M 150W</b> HIGH BAY LIGHTING	LED-8034M50	LED-8034M50 (120V)	Up to 19344	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
	LED-8034M50-HV (480V)	LED-8034M50-HV (347V)	Up to 19022	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
<b>LED-8050M 300W</b> HIGH BAY LIGHTING	LED-8050M50	LED-8050M50 (120V)	Up to 34153	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"
	LED-8050M50-HV (480V)	LED-8050M50-HV (347V)	Up to 33533	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"

VOLTAGE:  120-277VAC  347VAC • >80 CRI • 50,000 HOUR RATED LIFE • 5 YEAR WARRANTY



A simple upgrade to your existing high bay fixtures that can be done today!



## HIGH BAY RETROFITS

Ideal for use in:

- Large retail spaces
- Industrial spaces
- Auditoriums
- Gymnasiums
- Warehouses
- Factories

### Retrofits into most popular high bay fixtures



**100W**  
**LED-8036M**

Replaces up to  
250W



**140W**  
**LED-8030M\***

Replaces up to  
400W



**140W**  
**LED-8032M\***

Replaces up to  
400W

**Aims light upward,  
sideways, and down**

**Total downlight  
for ultra-high ceilings**

Ask about our metal halide ballast compatible models

\* Design Patent  
D723,194

\* Design Patent  
29/519,210

DESCRIPTION			LUMENS	POWER USED	REPLACES	BASE	CCT			DIMENSIONS
<b>LED-8036M 100W</b> HIGH BAY LIGHTING	LED-8036M40-A	LED-8036M40-A (120V) LED-8036M40C-A (347V)	Up to 10902	100W	250W	EX39	4000K	✓	✓	7.6" x 7.9"
	LED-8036M57-A	LED-8036M57-A (120V) LED-8036M57C-A (347V)	Up to 11015	100W	250W	EX39	5700K	✓	✓	7.6" x 7.9"
<b>LED-8030M 140W</b> HIGH BAY LIGHTING	LED-8030M40-A	LED-8030M40-A (120V) LED-8030M40C-A (347V)	Up to 15763	140W	400W	EX39	4000K	✓	✓	9.2" x 9.1"
	LED-8030M57A	LED-8030M57-A (120V) LED-8030M57C-A (347V)	Up to 15966	140W	400W	EX39	5700K	✓	✓	9.2" x 9.1"
<b>LED-8032M 140W</b> HIGH BAY LIGHTING	LED-8032M40-A	LED-8032M40-A (120V) LED-8032M40C-A (347V)	Up to 16668	140W	400W	EX39	4000K	✓	✓	9.4" x 9.1"
	LED-8032M57-A	LED-8032M57-A (120V) LED-8032M57C-A (347V)	Up to 16923	140W	400W	EX39	5700K	✓	✓	9.4" x 9.1"
<b>LED-8034M 150W</b> HIGH BAY LIGHTING	LED-8034M50	LED-8034M50 (120V)	Up to 19344	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
	LED-8034M50-HV (480V)	LED-8034M50-HV (347V)	Up to 19022	150W	400W	EX39	5000K	✓	✓	6.02" x 2.76"
<b>LED-8050M 300W</b> HIGH BAY LIGHTING	LED-8050M50	LED-8050M50 (120V)	Up to 34153	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"
	LED-8050M50-HV (480V)	LED-8050M50-HV (347V)	Up to 33533	300W	1000W	EX39	5000K	✓	✓	12.6" x 12.4"

VOLTAGE:  120-277VAC  347VAC • >80 CRI • 50,000 HOUR RATED LIFE • 5 YEAR WARRANTY