



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED80HIDHEX39850 80W Led Hid RPL 50K Hor Rot Base Expandable

Keystone Technologies

Catalog Number	LED80HIDHEX39850
Manufacturer	Keystone Technologies
Description	Led Hid Replacement Lamp, 80W, EX39 Base, 5000K, 120-277V Input, Designed For Horizontal Application With Fold-Out Led Assemblies, Direct Drive (Gen 3) Smart Port Enabled
Weight per unit	3.7 (lbs/each)
Product Category	20170829135410

Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP40
lumens	12000
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	80
Wire Type	N/A

Material, Color, and Finish

Base Type	EX39
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Construction	N/A
Description	80W LED HID RPL 50K HOR ROT BASE EXPANDABLE
extra long description	Key KT-LED80HID-H-EX39-850-D /G3-DP
Long Description	LED HID REPLACEMENT LAMP, 80W, EX39 BASE, 5000K, 120-277V INPUT, DESIGNED FOR HORIZONTAL APPLICATION WITH FOLD-OUT LED ASSEMBLIES, DIRECT DRIVE (GEN 3) SMART PORT ENABLED
Product Type	80W, 11650 Lumen, 320W MH Equiv., Mogul Base, Redesigned Hea



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654123585
Manufacturers Part Number	KT-LED80HID-H-EX39-850-D /G3-D
UPC	843654123585

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
----------------------	-------------------------------

Packaging

Carton	1
Weight Per each	3.66

Uses, Certifications, and Standards

Energy Star	Y
-------------	---