



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LGE3350FAG Lge 3 Pole 350A Fixed Thermal Adjustable Mag BRKR

Eaton Corp

Catalog Number	LGE3350FAG
Manufacturer	Eaton Corp
Description	Eaton Series G Molded Case Circuit Breaker, LG-Frame, LG, Fixed Thermal, Adjustable Magnetic Trip, Three-Pole, 350 A, 65 Kaic At 240 Vac, 35 Kaic At 480 Vac, 18 Kaic At 600 Vac, Line and Load, Metric, 50/60 HZ, 80% Rated
Weight per unit	16.0 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

Features

Current Rating	350 A
dimensions	4.0900 IN X 5.4800 IN X 5.4800 IN
frame	LG
interrupt rating	35 kAIC at 480 Vac18 kAIC at 600 Vac65 kAIC at 240 Vac
media	Yes
Poles	Three-pole
Trip Type	Fixed thermal, adjustable magnetic

Descriptions

Description	LGE 3 POLE 350A FIXED THERMAL ADJUSTABLE MAG BRKR
extra long description	ETN LGE3350FAG LGE 3P 350 A Fixed t
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G molded case circuit breaker, LG-frame, LG, Fixed thermal, adjustable magnetic trip, Three-pole, 350 A, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, 18 kAIC at 600 Vac, Line and load, Metric, 50/60 Hz, 80% rated
Product Type	Lge 3P 350 A Fixed Thermal Adj Mag BRK

Manufacturer Information

Brand	Eaton
GTIN	00782116142392
Manufacturers Part Number	LGE3350FAG
UPC	782116142392



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type Molded case circuit breaker

Packaging

Carton 1

Weight Per each 16

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Frequency Rating 50 to 60 Hz

standard UL Listed,CSA Certified,IEC Rated,CE Marked