

Eaton LKS-10

Catalog Number: LKS-10

Eaton Bussmann series LKS fuse link, 600V, 10A, Class H, K5



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series LKS fuse link	LKS-10
UPC	EAN
051712140102	5027590466332
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	0.12 lb
Warranty	Compliances
Not Applicable	RoHS Compliant

Product specifications

Type

Non Current-limiting, renewable

Special features

Super Lag, Time Lag

Application

Industrial and commercial structures

Amperage Rating

10 A

Class

Class H

Class K5

Fuse indicator

Non-indicating

Voltage rating

600 V

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[LKS-10~SUPER LAG RENEWABLE LINK](#)

Specifications and datasheets

[Eaton Specification Sheet - LKS-10](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton LKS-10

Catalog Number: LKS-10

Eaton Bussmann series LKS fuse link, 600V, 10A, Class H, K5



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series LKS fuse link	LKS-10
UPC	EAN
051712140102	5027590466332
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	0.12 lb
Warranty	Compliances
Not Applicable	RoHS Compliant

Product specifications

Type

Non Current-limiting, renewable

Special features

Super Lag, Time Lag

Application

Industrial and commercial structures

Amperage Rating

10 A

Class

Class H

Class K5

Fuse indicator

Non-indicating

Voltage rating

600 V

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[LKS-10~SUPER LAG RENEWABLE LINK](#)

Specifications and datasheets

[Eaton Specification Sheet - LKS-10](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)