

Eaton LKS-150

Catalog Number: LKS-150

Eaton Bussmann series LKS fuse link, 600V, 150A, Class H, K5

General specifications

Product Name	Catalog Number
Eaton Bussmann series LKS fuse link	LKS-150
UPC	Product Length/Depth
051712141505	0.001 in
Product Height	Product Width
0.001 in	0.001 in
Product Weight	Warranty
0.7 lb	Not Applicable

Compliances
RoHS Compliant



Photo is representative

Product specifications

Type

Non Current-limiting, renewable

Special features

Super Lag, Time Lag

Application

Industrial and commercial structures

Amperage Rating

150 A

Class

Class H

Class K5

Fuse indicator

Non-indicating

Voltage rating

600 V

Resources

Catalogs

[LKS-150~SUPER LAG RENEW. FUSE LINK](#)

[Bussmann series complete full line catalog no. 1007](#)

Specifications and datasheets

[Eaton Specification Sheet - LKS-150](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton LKS-150

Catalog Number: LKS-150

Eaton Bussmann series LKS fuse link, 600V, 150A, Class H, K5

General specifications

Product Name	Catalog Number
Eaton Bussmann series LKS fuse link	LKS-150
UPC	Product Length/Depth
051712141505	0.001 in
Product Height	Product Width
0.001 in	0.001 in
Product Weight	Warranty
0.7 lb	Not Applicable

Compliances
RoHS Compliant



Photo is representative

Product specifications

Type

Non Current-limiting, renewable

Special features

Super Lag, Time Lag

Application

Industrial and commercial structures

Amperage Rating

150 A

Class

Class H

Class K5

Fuse indicator

Non-indicating

Voltage rating

600 V

Resources

Catalogs

[LKS-150~SUPER LAG RENEW. FUSE LINK](#)

[Bussmann series complete full line catalog no. 1007](#)

Specifications and datasheets

[Eaton Specification Sheet - LKS-150](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)