

# Eaton LL67

Catalog Number: LL67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LL shape, 2"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	LL67
	UPC
	782274525303
Product Length/Depth	Product Height
8.13 in	4.13 in
Product Width	Product Weight
3.13 in	4.6 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

12

## Product specifications

### Shape

LL

### Trade size

2"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - LL67](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton LL67

Catalog Number: LL67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LL shape, 2"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	LL67
	UPC
	782274525303
Product Length/Depth	Product Height
8.13 in	4.13 in
Product Width	Product Weight
3.13 in	4.6 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

12

## Product specifications

### Shape

LL

### Trade size

2"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - LL67](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)