



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LPJ412SP 4-1/2A 600V J TD Fuse

Bussmann Fuses

Catalog Number	LPJ412SP
Manufacturer	Bussmann Fuses
Description	4-1/2A 600V Class J Low Peak Dual Element, Time Delay Fuse
Weight per unit	0.1900 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	4.5A
class	Class J
connection	Ferrule End X Ferrule End
dimensions	0.8100 IN X 0.8100 IN X 2.2500 IN
element	Dual
interrupt rating	300 kAIC at 600 Vac100 kAIC Vdc
Response Time	10 sec at 500%
Voltage Rating	600 Vac, 300 Vdc

Dimensions and Weight

Size	0.81 In Diameter X 2.25 In Length
------	-----------------------------------

Descriptions

Description	4-1/2A 600V J TD FUSE
extra long description	EFSE LPJ-4-1/2SP LOW-PEAK CLASS J T
Features	Bussmann's UL Class J fuse products extend both our Low-Peak family of products with our LPJ_SP and LPJ_SPI dual-element, time-delay fuses as well as our Limitron line offering fast-acting JKS fuses. The LPJ fuses provide industry leading 300,000 amp interrupting rating at 600Vac RMS Sym and 100kA Vdc while delivering a minimum of 10 seconds of 500 percent rated current ride-through performance which is ideal for sizing of high inrush loads. The LPJ products are available with optional permanent replace fu
Long Description	4-1/2A 600V Class J Low Peak Dual Element, Time Delay Fuse
Product Type	Low-Peak Class J T/D

Manufacturer Information

Brand	Eaton
GTIN	00051712522786
Manufacturers Part Number	LPJ412SP
UPC	051712522786



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Packaging

Carton	10
Weight Per each	0.19

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked,RoHS Compliant