

# Specifications

## Eaton LR47 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LR shape, 1-1/4"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	LR47 SA
<b>UPC</b>	782274528816
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	3.19 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	0.95 lb



*Powering Business Worldwide*

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

## Product specifications

SHAPE	LR
TRADE SIZE	1-1/4"
MATERIAL	Copper-free aluminum

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Form 7 catalog page</a>
CERTIFICATION REPORTS	<a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers UL certification</a> <a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 964 - Conduit Body Wire Pulling</a> <a href="#">IF 863 - Conduit Body Wire Pulling</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Condulet Form 7 Industrial Grade Conduit Bodies</a> <a href="#">Eaton Specification Sheet - LR47 SA</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Industrial Fittings Wire Fill Chart</a> <a href="#">Industrial Fittings Bend Radius and Cubic Capacity Chart</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton LR47 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, LR shape, 1-1/4"



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	LR47 SA
<b>UPC</b>	782274528816
<b>PRODUCT LENGTH/DEPTH</b>	6.5 in
<b>PRODUCT HEIGHT</b>	3.19 in
<b>PRODUCT WIDTH</b>	2.31 in
<b>PRODUCT WEIGHT</b>	0.95 lb



*Powering Business Worldwide*

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	12

## Product specifications

<b>SHAPE</b>	LR
<b>TRADE SIZE</b>	1-1/4"
<b>MATERIAL</b>	Copper-free aluminum

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Form 7 catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers UL certification</a> <a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 964 - Conduit Body Wire Pulling</a> <a href="#">IF 863 - Conduit Body Wire Pulling</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Condulet Form 7 Industrial Grade Conduit Bodies</a> <a href="#">Eaton Specification Sheet - LR47 SA</a>
<b>TECHNICAL SERVICE BULLETINS</b>	<a href="#">Industrial Fittings Wire Fill Chart</a> <a href="#">Industrial Fittings Bend Radius and Cubic Capacity Chart</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

