

Specifications

Eaton LR37

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 1"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	LR37
UPC	782274528403
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	2.75 in
PRODUCT WIDTH	1.88 in
PRODUCT WEIGHT	1.72 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	LR
TRADE SIZE	1"
MATERIAL	Feraloy iron alloy

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification Condulet Form 7 Conduit Outlet Bodies and Covers UL certification
INSTALLATION INSTRUCTIONS	IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Condulet Form 7 Industrial Grade Conduit Bodies Eaton Specification Sheet - LR37
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton LR37

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 1"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	LR37
UPC	782274528403
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	2.75 in
PRODUCT WIDTH	1.88 in
PRODUCT WEIGHT	1.72 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	LR
TRADE SIZE	1"
MATERIAL	Feraloy iron alloy

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification Condulet Form 7 Conduit Outlet Bodies and Covers UL certification
INSTALLATION INSTRUCTIONS	IF 964 - Conduit Body Wire Pulling IF 863 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Condulet Form 7 Industrial Grade Conduit Bodies Eaton Specification Sheet - LR37
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

