



# Decorator Devices Decorator Dimmers – Slide



**Ergonomic design and solid, quality feel** combine for smooth, easy operation and precise control.

**Electromagnetic and radio-frequency interference protection** built in.

**Sleek, sculpted contemporary design.** No dirt-catching crevices.

**Patented Snap-In Light Module** (sold separately) transforms the dimmer into an illuminated dimmer. See Page M-17 for information.



**LS600-PLA**


**Tough, impact-resistant thermoplastic housing** makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster® wall plate available for all models.

**Preset "On/Off" switch** automatically returns controlled lights to preset level without readjusting dimmer setting.


**Exclusive, screw-pressure-plate back wire terminals** save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.



**LS600-LA**



**LS600-PLA**



**LS1000-PLA**

Catalog Number		Description	Ratings	Color
Single Pole	Three-Way			
<b>600W Incandescent Slide Dimmers*</b>				
LS600-I LS600-W LS600-LA		Non-Preset	600W max.	Ivory White Light Almond
LS600-PI LS600-PW LS600-PLA	LS603-PI LS603-PW LS603-PLA	Preset	600W max.	Ivory White Light Almond
<b>1000W Incandescent Slide Dimmers*</b>				
LS1000-I LS1000-W LS1000-LA		Non-Preset	1000W max.	Ivory White Light Almond
LS1000-PI LS1000-PW LS1000-PLA	LS1003-PI LS1003-PW LS1003-PLA	Preset	1000W max.	Ivory White Light Almond
<b>600VA Low-Voltage Magnetic Slide Dimmers**</b>				
LSLV600-I LSLV600-W LSLV600-LA		Non-Preset	600VA max.	Ivory White Light Almond
LSLV600-PI LSLV600-PW LSLV600-PLA	LSLV603-PI LSLV603-PW LSLV603-PLA	Preset	600VA max.	Ivory White Light Almond

\* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: LS600-IV.

\*\* Available in boxed packaging only.

Catalog Number	Description	Color
<b>Accessories</b>		
LRK-IV LRK-WV LRK-LAV	Replacement Knobs for Decorator Dual Slides	Ivory White Light Almond
LLRK-IV LLRK-WV LLRK-LAV	Large Replacement Knobs for Decorator Single Slides	Ivory White Light Almond

Max. Load Rating	Fins Removed	
	One Side	Two Side
<b>De-Rating Chart</b>		
LS600, LS603	No De-Rating Required	
LS1000P, LS1003P	900W	750W
LS1000	850W	700W

For wiring diagrams, see Page U-20.

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.