



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DHG Non-III Mom PB Sil-BZL Extd GRN

Eaton Corp

Catalog Number	M22DHG
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, 22.5 MM, Extended, Momentary, Non-Illuminated, Bezel: Silver, Button: Green, IP67, IP69K, Nema 4X, 13, 5, 000, 000 Million Mechanical Operations
Weight per unit	0.0500 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Extended, Button
operating cycles	5 million

Dimensions and Weight

Depth	0.5
Height	0.1
Size	22.5 mm
Width	0.5

Descriptions

Description	NON-ILL MOM PB SIL-BZL EXTD GRN
extra long description	ETN M22-DH-G NON-ILL MOM PB SIL-BZL
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, 22.5 mm, Extended, Momentary, Non-illuminated, Bezel: Silver, Button: Green, IP67, IP69K, NEMA 4x, 13, 5,000,000 Million mechanical operations
Product Type	Non-III Mom PB Sil-BZL Extd GRN

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685276014
Manufacturers Part Number	M22-DH-G
Model	Modular pushbutton
UPC	786685276014

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.05

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
standard	CCC Marked, CSA Certified, Lloyd's Register Certified, GoST-R, CE Marked, Bureau Veritas