



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## M22DHRK11P Red Ext Mom PB 1NO/1NC LGND PLS Pop

Eaton Corp

Catalog Number	M22DHRK11P
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton M22 Pushbutton, Complete Device, 22.5 MM, Extended, Momentary, Non-Illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, Nema 4X
Weight per unit	0.0800 (lbs/each)
Product Category	Push Button Complete Assemblie

### Features

actuator	Button, Extended
Contact Configuration	1 NO-1 NC

### Dimensions and Weight

Depth	0.5
Height	4
Size	22.5 mm
Width	5

### Descriptions

Description	RED EXT MOM PB 1NO/1NC LGND PLS POP
extra long description	ETN M22-DH-R-K11-P RED EXT MOM PB,
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton M22 Pushbutton, Complete Device, 22.5 mm, Extended, Momentary, Non-illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, NEMA 4X
Product Type	Red Ext Mom PB, 1NO/1NC, LGND PLS Pop

### Manufacturer Information

Brand	Eaton
GTIN	00786685382524
Manufacturers Part Number	M22-DH-R-K11-P
Model	Modular pushbutton
UPC	786685382524

### Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.08

## Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
standard	CSA Certified, Lloyd's Register Certified, CCC Marked, CE Marked, GoST-R, Bureau Veritas