ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

M22DLHRK11RP Red Ext Ill Mom PB 1NO/1NC 12-30VAC/DC Led LGND PL

Eaton Corp

Catalog Number	M22DLHRK11RP
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Complete Device, 22.5 MM, Extended, Momentary, Illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, Nema 4X, 13, 12-30 Vac/DC
Weight per unit	0.1100 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Button, Extended
Contact Configuration	1 NO-1 NC
Voltage Rating	12-30 Vac/dc

Dimensions and Weight

Depth	1.46
Height	3.45
Size	22.5 mm
Width	1.18

Descriptions

Description	RED EXT ILL MOM PB 1NO/1NC 12-30VAC/DC LED LGND PL
extra long description	ETN M22-DLH-R-K11-R-P RED EXT ILL M
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, Complete Device, 22.5 mm, Extended, Momentary, Illuminated, Bezel: Silver, Button: Red, 1NO-1NC, IP67, IP69K, NEMA 4X, 13, 12-30 Vac/dc
Product Type	Red Ext Ill Mom PB, 1NO/1NC, 12-30VAC/DC
Special Features	M22 series

Manufacturer Information

Brand	Eaton
GTIN	00786685382548
Manufacturers Part Number	M22-DLH-R-K11-R-P
Model	Modular pushbutton
UPC	786685382548

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
environmental conditions	IP67, IP69K, NEMA 4X, NEMA 13
standard	CCC Marked,Lloyd's Register Certified,CSA Certified,GoST-R,Bureau Veritas,CE Marked