



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22LGG Ind LGHT GRN 12-30VAC/DC Eaton Corp

Catalog Number	M22LGG
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Green Indicating Light, Flush, IP67, IP69K, Nema 4X, 13, Illuminated, 100, 000 Hours Of Operation, 12-30 Vac/DC
Weight per unit	0.0500 (lbs/each)
Product Category	Pilot Light Complete Assemblie

Features

dimensions	2.0000 IN X 2.0000 IN X 1.0000 IN
Voltage Rating	12-30 Vac/dc

Material, Color, and Finish

Lens Color	GREEN
------------	-------

Descriptions

Description	IND LGHT GRN 12-30VAC/DC
extra long description	ETN M22-L-G-G IND LGHT GRN 12-30VAC
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, Green Indicating Light, Flush, IP67, IP69K, NEMA 4X, 13, Illuminated, 100, 000 Hours of operation, 12-30 Vac/dc
Product Type	Ind LGHT GRN 12-30VAC/DC

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685278575
Manufacturers Part Number	M22-L-G-G
UPC	786685278575

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Modular pushbutton

Packaging

Carton	1
Weight Per each	0.05



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

Lloyd's Register Certified,CCC Marked,CSA Certified,Bureau
Veritas,CE Marked,GoST-R