



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22SDDLX7X7 Non-FLSH III DBL PB BLK-BZL BLK Top BLK

Eaton Corp

Catalog Number	M22SDDLX7X7
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Double Pushbutton Operator, 22.5 MM, Extended, Momentary, Illuminated, Bezel: Black, Button: Top/Bottom: Black, Inscription: Top Up Arrow, Bottom Down Arrow/ X7, IP66, Nema 4X, 13, Light 100, 000 Hours
Weight per unit	0.1000 (lbs/each)
Product Category	Push Button Complete Assembleie

Features

actuator	Extended, Dual button
operating cycles	Light: 100,000, button: 200,000

Dimensions and Weight

Depth	1
Height	0.05
Size	22.5 mm
Width	1

Descriptions

Description	NON-FLSH ILL DBL PB BLK-BZL BLK TOP BLK
extra long description	ETN M22S-DDL-S-X7-X7 NEMA 4X, 13, L
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 Modular Double Pushbutton Operator, 22.5 mm, Extended, Momentary, Illuminated, Bezel: Black, Button: Top/bottom: Black, Inscription: Top up arrow, Bottom down arrow/ X7, IP66, NEMA 4X, 13, Light 100,000 hours
Product Type	Nema 4X, 13, Light 100, 000 Hours

Manufacturer Information

Brand	Eaton
GTIN	00786685272146
Manufacturers Part Number	M22S-DDL-S-X7-X7
Model	Pushbutton accessory
UPC	786685272146



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MINATURE PILOT DEVICES.22MM

Packaging

Carton 1

Weight Per each 0.1

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

environmental conditions IP66, NEMA 4X, NEMA 13

standard CCC Marked,Lloyd's Register Certified,CSA Certified,Bureau
Veritas,CE Marked,GoST-R