



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22SSTGB7 Legend Plate Etched

Eaton Corp

Catalog Number	M22SSTGB7
Manufacturer	Eaton Corp
Description	Eaton M22 Pushbutton Legend Plate, M22 Modular Pushbutton Legend Plate, Complete, 22.5 MM, Button: Black, Inscription: Run/ GB7, IP66, Nema 4X, 13
Weight per unit	0.0100 (lbs/each)
Product Category	Legend Plates

Features

dimensions	2.0000 IN X 2.0000 IN X 1.3800 IN
------------	-----------------------------------

Dimensions and Weight

Size	22.5 mm
------	---------

Descriptions

Description	LEGEND PLATE ETCHED
extra long description	ETN M22S-ST-GB7 LEGEND PLATE ETCHED
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 pushbutton legend plate, M22 Modular Pushbutton Legend Plate, Complete, 22.5 mm, Button: Black, Inscription: RUN/ GB7, IP66, NEMA 4X, 13
Product Type	Legend Plate Etched
Special Features	Legend plate Holder with Insert

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685277370
Manufacturers Part Number	M22S-ST-GB7
UPC	786685277370

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
Type	Pushbutton accessory

Packaging

Carton	1
Weight Per each	0.01



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

standard

Lloyd's Register Certified, CSA Certified, CCC Marked, Bureau

Veritas, CE Marked, GoST-R