



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22SDHG Non-III Mom PB BLK-BZL Extd GRN Eaton Corp

Catalog Number	M22SDHG
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton M22 Modular Pushbutton Operator, 22.5 MM, Extended, Momentary, Non-Illuminated, Bezel: Black, Button: Green, IP67, IP69K, Nema 4X, 13, 5, 000, 000 Million Mechanical Operations
Weight per unit	0.0400 (lbs/each)
Product Category	Push Button Complete Assembleie

Features

actuator	Extended, Button
operating cycles	5 million

Dimensions and Weight

Depth	1
Height	6
Size	22.5 mm
Width	5

Descriptions

Description	NON-ILL MOM PB BLK-BZL EXTD GRN
extra long description	ETN M22S-DH-G NON-ILL MOM PB BLK-BZ
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton M22 Modular Pushbutton Operator, 22.5 mm, Extended, Momentary, Non-illuminated, Bezel: Black, Button: Green, IP67, IP69K, NEMA 4x, 13, 5,000,000 Million mechanical operations
Product Type	Non-III Mom PB BLK-BZL Extd GRN

Manufacturer Information

Brand	Eaton
GTIN	00786685275413
Manufacturers Part Number	M22S-DH-G
Model	Modular pushbutton
UPC	786685275413



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MINATURE PILOT DEVICES.22MM

Packaging

Carton 1

Weight Per each 0.04

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -
..... Stationary Machinery and Equipment Outside Factory - Other

environmental conditions IP67, IP69K, NEMA 4X, NEMA 13

standard Lloyd's Register Certified, CSA Certified, CCC
..... Marked, GoST-R, CE Marked, Bureau Veritas