



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## M4C250342 Heat-Shrink Labels 0.25 " Dia BK/WT

Brady Worldwide, Inc.

Catalog Number	M4C250342
Manufacturer	Brady Worldwide, Inc.
Description	Permasleeve® Heat-Shrink Labels Polyolefin 0.25 In Dia Black On White
Weight per unit	0.2750 (lbs/each)
Product Category	20230706151459

### Features

Material	Heat-shrink Polyolefin
Quantity	Cartridge of 7 Feet
Shrink Ratio	3:1
Temperature Range	-67 °F - 275 °F
Wire Size	0.25 in Dia x 7 ft L

### Material, Color, and Finish

Finish	Matte
Legend Color	Black on White

### Dimensions and Weight

Diameter	0.25
Height	0.439 in
Length	7 ft
Size	0.439 in H

### Descriptions

Description	HEAT-SHRINK LABELS 0.25 " DIA BK/WT
extra long description	BRADY M4C-250-342 Heat-Shrink Lbls
Features	Permanently mark wires with the durable PermaSleeve® PS heat-shrink polyolefin sleeve label material (B-342). Designed for use with a durable Brady handheld label printer.
Long Description	PermaSleeve® Heat-Shrink Labels Polyolefin 0.25 in Dia Black on White
Product Type	Heat-Shrink LBLS 0.25 In Dia BK/WT
Special Features	Heat Shrink

### Manufacturer Information

Brand	Brady®
GTIN	00888434591437
Manufacturers Part Number	M4C-250-342
UPC	888434591437



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	SLEEVE

## Packaging

Carton	1
Weight Per each	0.275

## Uses, Certifications, and Standards

Application	Electrical Labeling;Wire and Cable Labeling
standard	ASTM D 2671;ASTM E 162;ASTM E 662;ASTM G 155;MIL-STD-202;SAE-AMS-DTL-23053;SAE-AS-81531;UL Recognized