



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M6250175342WT Heat-Shrink Labels 0.25" Dia X 1.75" WH

Brady Worldwide, Inc.

Catalog Number	M6250175342WT
Manufacturer	Brady Worldwide, Inc.
Description	Permasleeve® Heat-Shrink Labels 0.25 In Dia WT 1.75 In RL/100
Weight per unit	0.2310 (lbs/each)
Product Category	Tools & Testers

Features

Material	Heat-shrink Polyolefin
Number of Markers	100
Quantity	Roll of 100 Each
Shrink Ratio	3:1
Temperature Range	-67 °F - 275 °F
Wire Size	0.25 in Dia x 1.75 in W

Material, Color, and Finish

Finish	Matte
Legend Color	White

Dimensions and Weight

Diameter	0.25
Height	0.444 in
Size	0.444 in H x 1.75 in W
Width	1.75 in

Descriptions

Description	HEAT-SHRINK LABELS 0.25" DIA X 1.75" WH
extra long description	BRADY M6-250-175-342-WT Heat-Shrink
Features	Designed for rigorous wire marking applications, PermaSleeve® Heat Shrink Polyolefin (B-342) labels combine speed, ease of use, and permanence to create high quality labeling.
Long Description	PermaSleeve® Heat-Shrink Labels 0.25 in Dia WT 1.75 in RL/100
Product Type	Heat-Shrink LBLs 0.25DIA WT 1.75" RL/100
Special Features	Heat Shrink

Manufacturer Information

Brand	Brady®
GTIN	00888434595565
Manufacturers Part Number	M6-250-175-342-WT
UPC	888434595565



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	SLEEVE

Packaging

Carton	1
Weight Per each	0.231

Uses, Certifications, and Standards

Application	Electrical Labeling;Wire and Cable Labeling
standard	ASTM D 2671;ASTM E 162;ASTM E 662;ASTM G 155;MIL-STD-202;SAE-AMS-DTL-23053;SAE-AS-81531;UL Recognized