



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MDA15R 15A 250V 1/4\"/>

Bussmann Fuses

Catalog Number	MDA15R
Manufacturer	Bussmann Fuses
Description	Eaton Mda Series Time-Delay Fuse 15A, 250 Vac, 32 VDC (Self Certified), 10 Kaic At 125 Vac
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	15 A
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	10 kAIC at 125 Vac750 AIC at 250 Vac
Material	Ceramic tubeNickel-plated brass end cap construction
Response Time	60 min at 135%, 120 sec at 200%
Voltage Rating	250 Vac, 32 Vdc (self certified)

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	15A 250V 1/4\"/>
extra long description	EFSE MDA-15-R BUSS SMALL DIMENSION
Features	Eaton's Bussmann Division develops and manufactures critical circuit protection, power management and electrical safety products designed to provide innovative circuit and power electronics protection, serving the commercial, data center, electrical vehicle, food and beverage, and other markets.
Long Description	Eaton MDA Series Time-delay fuse 15A, 250 Vac, 32 Vdc (self certified), 10 kAIC at 125 Vac
Product Type	Buss Small Dimension Fuse
Special Features	Ceramic tube

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712645201
Manufacturers Part Number	MDA-15-R
UPC	051712645201

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Time-delay fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked