



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MDA20R 20A 250V 3AB - 1/4\"X1-1 *Bussmann Fuses*

Catalog Number	MDA20R
Manufacturer	Bussmann Fuses
Description	Eaton Mda Series Time-Delay Fuse 20A, 250 Vac, 125 VDC, 32 VDC (Self Certified), 1.5 Kaic At 250 Vac
Weight per unit	0.4000 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	20 A
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	1.5 kAIC at 250 Vac10 kAIC at 125 Vac/dc
Material	Nickel-plated brass end cap constructionCeramic tube
Response Time	60 min at 135%, 120 sec at 200%
Voltage Rating	250 Vac, 125 Vdc, 32 Vdc (self certified)

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	20A 250V 3AB - 1/4\"X1-1
extra long description	EFSE MDA-20-R ROHS COMPLIANT
Features	Eaton's Bussmann Division develops and manufactures critical circuit protection, power management and electrical safety products designed to provide innovative circuit and power electronics protection, serving the commercial, data center, electrical vehicle, food and beverage, and other markets.
Long Description	Eaton MDA Series Time-delay fuse 20A, 250 Vac, 125 Vdc, 32 Vdc (self certified), 1.5 kAIC at 250 Vac
Product Type	Rohs Compliant
Special Features	Ceramic tube

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712542494
Manufacturers Part Number	MDA-20-R
UPC	051712542494

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Time-delay fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,CE Marked