



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MSCL0P153MIV Maestro 150W Led Occupancy Multi Ivory

Lutron

Catalog Number	MSCL0P153MIV
Manufacturer	Lutron
Description	Maestro Occupancy Led+ Passive Infrared Occupancy/Vacancy Sensor That Automatically Controls The Lights In An Area In Ivory
Weight per unit	0.4000 (lbs/each)
Product Category	Lighting Dimmers

### Features

body	Plastic
load	600 W incandescent/halogen/140 W CFL/LED
media	Yes
sensing range	900 ft2 (82 m2) major motion coverage/400 ft2 (36 m2) minor motion coverage
supply voltage	120

### Material, Color, and Finish

Color	Ivory
Finish	Gloss



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	MAESTRO 150W LED OCCUPANCY MULTI IVORY
extra long description	LUT MSCL-OP153M-IV MAESTRO LED+ PIR
Features	The Lutron Maestro LED+ Motion Sensor Dimmer Switch works just like a Lutron Maestro dimmer, with the addition of Lutron's advanced motion sensing technology to automatically and gradually turn the lights on and off. The LED+ Motion Sensor Dimmer Switch is rated for 150W dimmable LED or 600W Incandescent/Halogen bulbs. Install in a single pole, 3-way with existing switch, or with Maestro companion dimmers (MA-R/MSC-AD) to dim from up to 9 locations. Use the raise/lower buttons to adjust the brightness for
Long Description	Maestro occupancy LED+ passive infrared occupancy/vacancy sensor that automatically controls the lights in an area in ivory
Product Type	Maestro Led+ Pir Occ Sensor Box Ivory
Special Features	Passive infrared sensors that automatically control the lights in an area. These sensors detect heat from occupants moving within an area to determine when the space is occupied. Combines a Maestro LED+ fine motion detection. 180 degree sensor field-of-view. Up to 30 ft x 30 ft (9 m x 9 m) [900 ft2 (81 m2)] major motion coverage and 20 ft x 20 ft (6 m x 6 m) [400 ft2 (36 m2)] minor motion coverage. Can be set to auto-on/auto-off or manual-on/auto-off. Adjustable timeout (1, 3, 5, 15, or 30 minutes) and h

## Manufacturer Information

Brand	Lutron
GTIN	00784276054690
Manufacturers Part Number	MSCL0P153MIV
UPC	784276054690

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Occupancy sensor dimmer, multi-location/3-way/single-pole

## Packaging

Carton	1
Package	24
Weight Per each	0.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL, Title 20/24 certified