



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MSCL0P153MWH Maestro 150W Led Occupancy Multi White

Lutron

Catalog Number	MSCL0P153MWH
Manufacturer	Lutron
Description	Maestro Occupancy Led+ Passive Infrared Occupancy/Vacancy Sensor That Automatically Controls The Lights In An Area In White
Weight per unit	0.3400 (lbs/each)
Product Category	Lighting Dimmers

Features

body	Plastic
load	600 W incandescent/halogen/140 W CFL/LED
media	Yes
sensing range	900 ft ² (82 m ²) major motion coverage/400 ft ² (36 m ²) minor motion coverage
supply voltage	120

Material, Color, and Finish

Finish	Gloss
--------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	MAESTRO 150W LED OCCUPANCY MULTI WHITE
extra long description	LUT MSCL-OP153M-WH MAESTRO LED+ PIR
Features	The Lutron Maestro LED+ Motion Sensor Dimmer Switch works just like a Lutron Maestro dimmer, with the addition of Lutron's advanced motion sensing technology to automatically and gradually turn the lights on and off. The LED+ Motion Sensor Dimmer Switch is rated for 150W dimmable LED or 600W Incandescent/Halogen bulbs. Install in a single pole, 3-way with existing switch, or with Maestro companion dimmers (MA-R/MSC-AD) to dim from up to 9 locations. Use the raise/lower buttons to adjust the brightness for
Long Description	Maestro occupancy LED+ passive infrared occupancy/vacancy sensor that automatically controls the lights in an area in white
Product Type	Maestro Led+ Pir Occ Sensor Box White
Special Features	Passive infrared sensors that automatically control the lights in an area. These sensors detect heat from occupants moving within an area to determine when the space is occupied. Combines a Maestro LED+ dimmer with an occupancy sensor. Controls CFL, LED, incandescent, and halogen load types. Passive infrared motion detection with exclusive Lutron XCT Technology for fine motion detection. 180 degree sensor field-of-view. Up to 30 ft x 30 ft (9 m x 9 m) [900 ft ² (81 m ²)] major motion coverage and 20 ft x 2

Manufacturer Information

Brand	Lutron
GTIN	00784276054843
Manufacturers Part Number	MSCL-OP153M-WH
UPC	784276054843

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Occupancy sensor dimmer, multi-location/3-way/single-pole

Packaging

Carton	1
Weight Per each	0.34



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL, Title 20/24 certified