



**SINGLE GANG MULTI-CONFIGURATION FLIP COVERS**

**One Gang Universal Metal Flip Covers  
Vertical/Horizontal 12-in-1**

**D11**



Catalog #: MX1050Z

**APPLICATIONS**

For use whenever weatherproof protection is required for an outdoor receptacle or switch.  
N/A

**PRODUCT FEATURES**

- Heavy duty die-cast metal construction
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Pre-configured for GFCI with patented knockout technology for alternate devices
- Includes attached gasket and mounting hardware
- Premium powder coat finish
- Lockable tab

**UL LISTED**

File E212332

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A)

**US PATENTS**

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

**GENERAL PRODUCT INFORMATION**

Color: White

**CONFIGURATION**

Gangs: 1

**PRODUCT MEASUREMENTS**

Wt. Ea. (Lbs.): 0.305

**PACKAGING**

Package Type: Shrink  
 Std. Pkg.: 20  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 30.50  
 Ship Carton Length (in.): 16.13  
 Ship Carton Width (in.): 3.75  
 Ship Carton Height (in.): 7.50  
 Ctn Weight (Lbs.): 6.10  
 Pallet Qty: 3000.00  
 UPC Number: 092326110662  
 I2of5: 30092326110663



**SINGLE GANG MULTI-CONFIGURATION FLIP COVERS**

**One Gang Universal Metal Flip Covers  
Vertical/Horizontal 12-in-1**

**D11**



Catalog #: MX1050Z

**APPLICATIONS**

For use whenever weatherproof protection is required for an outdoor receptacle or switch.  
N/A

**PRODUCT FEATURES**

- Heavy duty die-cast metal construction
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Pre-configured for GFCI with patented knockout technology for alternate devices
- Includes attached gasket and mounting hardware
- Premium powder coat finish
- Lockable tab

**UL LISTED**

File E212332

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A)

**US PATENTS**

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

**GENERAL PRODUCT INFORMATION**

Color: White

**CONFIGURATION**

Gangs: 1

**PRODUCT MEASUREMENTS**

Wt. Ea. (Lbs.): 0.305

**PACKAGING**

Package Type: Shrink  
 Std. Pkg.: 20  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 30.50  
 Ship Carton Length (in.): 16.13  
 Ship Carton Width (in.): 3.75  
 Ship Carton Height (in.): 7.50  
 Ctn Weight (Lbs.): 6.10  
 Pallet Qty: 3000.00  
 UPC Number: 092326110662  
 I2of5: 30092326110663