


RaynGuard® Jumbo 2-Gang Weatherproof In-Use Cover

Catalog #:
MX6200



MX6200



FEATURE BENEFIT

Extra Deep, provides 3-1/2 inches of depth inside while in use



PRODUCT FEATURES

- Heavy duty die-cast aluminum construction
- Patented QuickFit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab (fits up to 1/8 in. shackable)
- Premium Powder Coat

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use

CERTIFICATIONS



NEMA 3R Rated
NEC - Extra Duty Rated

PRODUCT SPECIFICATIONS

UPC Number:	092326104838
Ea Length/Depth (in.):	3.48
Ea Width (in.):	5.12
Ea Height (in.):	6.12
Wt. Ea. (Lbs.):	0.972
Color:	Gray
Gangs:	2
Package Type:	Shrink
Package Contents:	1
Product UPC-A Labeled:	Yes

SHIPPING

12of5:	40092326104836
Standard Carton Qty:	4
Min Order Qty:	1
Ship Carton Length (in.):	14.76
Ship Carton Width (in.):	5.31
Ship Carton Height (in.):	6.69
Ship Carton Weight (Lbs.):	3.886
Pallet Qty:	504



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

TayMac
2520 E. University Dr.
Tempe, AZ 85281
800-526-5416
www.hubbell.com/taymac/en




Revision 1, July 2018

RaynGuard[®] Jumbo 2-Gang Weatherproof In-Use Cover

Catalog #:
MX6200



MX6200



FEATURE BENEFIT

Extra Deep, provides 3-1/2 inches of depth inside while in use



PRODUCT FEATURES

- Heavy duty die-cast aluminum construction
- Patented QuickFit keyhole mounting system allows installation in under a minute
- Includes attached gasket and mounting hardware
- Pre-configured for GFCI with patented Knockout technology for alternate devices
- Lockable tab (fits up to 1/8 in. shackable)
- Premium Powder Coat

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use

CERTIFICATIONS



NEMA 3R Rated

NEC - Extra Duty Rated

PRODUCT SPECIFICATIONS

UPC Number:	092326104838
Ea Length/Depth (in.):	3.48
Ea Width (in.):	5.12
Ea Height (in.):	6.12
Wt. Ea. (Lbs.):	0.972
Color:	Gray
Gangs:	2
Package Type:	Shrink
Package Contents:	1
Product UPC-A Labeled:	Yes

SHIPPING

12of5:	40092326104836
Standard Carton Qty:	4
Min Order Qty:	1
Ship Carton Length (in.):	14.76
Ship Carton Width (in.):	5.31
Ship Carton Height (in.):	6.69
Ship Carton Weight (Lbs.):	3.886
Pallet Qty:	504



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

TayMac
2520 E. University Dr.
Tempe, AZ 85281
800-526-5416
www.hubbell.com/taymac/en



Revision 1, July 2018