PASS & SEYMOUR®

radiant® Night Lights
15A, 120/125V




More light levels to meet the demands of every end user and installer.

NTL885TR, NTL873*CC, NTLFULL, NTLHORZ

Installing extra nighttime convenience, control and safety is made simple with Legrand's full line of radiant® night light devices. These night lights easily replace any standard receptacle and offer adjustable light levels, as well as an optional louver for even greater light-level control. And now as part of the radiant® collection, they offer a better fit, form and finish in every hallway, kitchen or nursery.

Features & Benefits

- **Two tamper-resistant outlets** — an industry exclusive.



Now with black "invisi-shutters" for an invisible effect preferred by end users.

NTL885TRWCC6

- **Part of the radiant® collection.**
- **Five adjustable light settings** including OFF.
- **Hidden sensor automatically controls night lights.**
- **Replace any standard receptacle.**
- **Ideal for hallways, kitchens and nurseries.**

NTL885TR*, NTLFULL*

- **Optional louver included** for added light-level control.


Compliance

cULus listed. Conform to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Maximum Working Voltage	125V
Maximum Current Interrupting	15A
Maximum Temperature Rise	30°C
Mechanical	
Terminal Identification	Terminal identification in accordance with UL20
Terminal Accommodation	Back and side wire terminals accommodate #12 and #14 AWG stranded and copper wire Push wire terminals accommodate #14 AWG
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL20 minimum rating

Materials	
Face	Thermoplastic
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.042 Zinc-Plated Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Mounting Screws	Steel plated



NTL873LACC6



NTLFULL



NTLHORZ

Warranty
1 Year

Ordering Information

Night Light with Two 15A Tamper-Resistant Receptacles and Adjustable Light Levels with optional louver included

	Rating				3rd Party Compliance
Catalog Number	**A**	**VAC**	**Color**	**NEMA Config. No.**	c UL us
NTL885TRICC6	15	120/125	Ivory	5-15R	•
NTL885TRWCC6	15	120/125	White	5-15R	•
NTL885TRLACC6	15	120/125	Light Almond	5-15R	•
NTL885TRBKCC6	15	120/125	Black	5-15R	•
NTL885TRNICC6	15	120/125	Nickel	5-15R	•

Night Light with Single Pole/3-Way Switch

	Rating			3rd Party Compliance
Catalog Number	**A**	**VAC**	**Color**	c UL us
NTL873ICC6	15	120/125	Ivory	•
NTL873WCC6	15	120/125	White	•
NTL873LACC6	15	120/125	Light Almond	•
NTL873BKCC6	15	120/125	Black	•
NTL873NICC6	15	120/125	Nickel	•

Full Night Light, Adjustable Light Levels, Tri-Color with optional louver included*

NTLFULLTCCC6	120/125	Ivory Light Almond Black	•
NTLHORZTCCC6	120/125	Ivory Light Almond Black	•

Full Night Light, Adjustable Light Levels with optional louver included*

NTLFULLWCC6	120/125	White	•
NTLHORZWCC6	120/125	White	•

*NTLHORZTCCC6 and NTLHORZWCC6 only used with louver.

2 Pole, 3 Wire



NEMA 5-15R

Vertical Markets

- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

Also available in the radiant® collection

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Paddle Switches
- Lighting & Fan Controls
- Timers
- Combination Devices
- USB Charging Devices
- Screwless Wall Plates
- Sensors
- Home Automation Controls

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20192 December 2016 ©2016 Legrand All Rights Reserved

PASS & SEYMOUR®

radiant® Night Lights
15A, 120/125V




More light levels to meet the demands of every end user and installer.

NTL885TR, NTL873*CC, NTLFULL, NTLHORZ

Installing extra nighttime convenience, control and safety is made simple with Legrand's full line of radiant® night light devices. These night lights easily replace any standard receptacle and offer adjustable light levels, as well as an optional louver for even greater light-level control. And now as part of the radiant® collection, they offer a better fit, form and finish in every hallway, kitchen or nursery.

Features & Benefits

- **Two tamper-resistant outlets** — an industry exclusive.



Now with black "invisi-shutters" for an invisible effect preferred by end users.

NTL885TRWCC6

- **Part of the radiant® collection.**
- **Five adjustable light settings** including OFF.
- **Hidden sensor automatically controls night lights.**
- **Replace any standard receptacle.**
- **Ideal for hallways, kitchens and nurseries.**

NTL885TR*, NTLFULL*

- **Optional louver included** for added light-level control.


Compliance

cULus listed. Conform to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Maximum Working Voltage	125V
Maximum Current Interrupting	15A
Maximum Temperature Rise	30°C
Mechanical	
Terminal Identification	Terminal identification in accordance with UL20
Terminal Accommodation	Back and side wire terminals accommodate #12 and #14 AWG stranded and copper wire Push wire terminals accommodate #14 AWG
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL20 minimum rating

Materials	
Face	Thermoplastic
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.042 Zinc-Plated Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Mounting Screws	Steel plated



NTL873LACC6



NTLFULL



NTLHORZ

Warranty
1 Year

Ordering Information

Night Light with Two 15A Tamper-Resistant Receptacles and Adjustable Light Levels with optional louver included

	Rating				3rd Party Compliance
Catalog Number	**A**	**VAC**	**Color**	**NEMA Config. No.**	c UL us
NTL885TRICC6	15	120/125	Ivory	5-15R	•
NTL885TRWCC6	15	120/125	White	5-15R	•
NTL885TRLACC6	15	120/125	Light Almond	5-15R	•
NTL885TRBKCC6	15	120/125	Black	5-15R	•
NTL885TRNICC6	15	120/125	Nickel	5-15R	•

Night Light with Single Pole/3-Way Switch

	Rating			3rd Party Compliance
Catalog Number	**A**	**VAC**	**Color**	c UL us
NTL873ICC6	15	120/125	Ivory	•
NTL873WCC6	15	120/125	White	•
NTL873LACC6	15	120/125	Light Almond	•
NTL873BKCC6	15	120/125	Black	•
NTL873NICC6	15	120/125	Nickel	•

Full Night Light, Adjustable Light Levels, Tri-Color with optional louver included*

NTLFULLTCCC6	120/125	Ivory Light Almond Black	•
NTLHORZTCCC6	120/125	Ivory Light Almond Black	•

Full Night Light, Adjustable Light Levels with optional louver included*

NTLFULLWCC6	120/125	White	•
NTLHORZWCC6	120/125	White	•

*NTLHORZTCCC6 and NTLHORZWCC6 only used with louver.

2 Pole, 3 Wire



NEMA 5-15R

Vertical Markets

- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

Also available in the radiant® collection

- GFCI Receptacles
- Standard & Tamper-Resistant Receptacles
- Paddle Switches
- Lighting & Fan Controls
- Timers
- Combination Devices
- USB Charging Devices
- Screwless Wall Plates
- Sensors
- Home Automation Controls

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20192 December 2016 ©2016 Legrand All Rights Reserved