



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NTSTVDVIV Nova T DV 8A 0-10V SP Ivory

Lutron

Catalog Number	NTSTVDVIV
Manufacturer	Lutron
Description	Nova T Dimmer, Electronic or Led Dimming With 0-10V Ballasts and Drivers, Single-Pole (Small Control), 120V/277V, 30MA In Ivory
Weight per unit	0.5500 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Slide
amperage rating	8
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
Poles	1
Switch Type	Slide
Voltage Rating	120 to 277
Wattage	2216

Material, Color, and Finish

Color	Ivory
Finish	Matte

Dimensions and Weight

Size	4.56 x 2.75;116 x 70
------	----------------------

Descriptions

Description	NOVA T DV 8A 0-10V SP IVORY
extra long description	LUT NTSTV-DV-IV NOVA T LINE SW 0-10
Long Description	Nova T Dimmer, Electronic or LED Dimming with 0-10V Ballasts and Drivers, Single-pole (small control), 120V/277V, 30mA in ivory
Product Type	Nova T Line SW 0-10V CTRL Ivory
Special Features	Controls 0-10V LED/fluorescent fixture loads, 30 mA max control current. Slide up to brighten, down to dim.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276071932
Manufacturers Part Number	NTSTV-DV-IV
UPC	784276071932

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Slide-to-off dimmer, single-pole

Packaging

Carton	1
Weight Per each	0.55

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CSA, NOM