



SWITCH & OUTLET BOX

P122R | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Gang Deep Switch and Outlet Box with Captive Mounting Nails on each end, with threaded mounting holes. Two Quick/Entries on each end. It is a durable, impact-resistant thermoplastic box and has innovative extras that cut installation time. Extra deep for dimmers, GFCIs and thermostats, yet suitable for 2x4 construction. 100 pack.



- Quick/Entry® feature speeds installation by eliminating need for tools, allows you to push stripped or unstripped non-metallic cable into a single-gang plastic box without removing knockouts.
- Threaded mounting holes.

SPECIFICATIONS

GENERAL INFO

Size: Deep
Product Series: Slater
Type: Box
Special Features: Quick/Entry

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121308

UR: No

DIMENSIONS

Depth (US): 3.375

Length (US): 3.75

Width (US): 2.25

Volume: 22.5

TECHNICAL INFORMATION

Material: Plastic

Mounting: Captive Mounting Nails

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant





SWITCH & OUTLET BOX

P122R | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Gang Deep Switch and Outlet Box with Captive Mounting Nails on each end, with threaded mounting holes. Two Quick/Entries on each end. It is a durable, impact-resistant thermoplastic box and has innovative extras that cut installation time. Extra deep for dimmers, GFCIs and thermostats, yet suitable for 2x4 construction. 100 pack.



- Quick/Entry® feature speeds installation by eliminating need for tools, allows you to push stripped or unstripped non-metallic cable into a single-gang plastic box without removing knockouts.
- Threaded mounting holes.

SPECIFICATIONS

GENERAL INFO

Size: Deep
Product Series: Slater
Type: Box
Special Features: Quick/Entry

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121308

UR: No

DIMENSIONS

Depth (US): 3.375

Length (US): 3.75

Width (US): 2.25

Volume: 22.5

TECHNICAL INFORMATION

Material: Plastic

Mounting: Captive Mounting Nails

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

