



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P8I Plastic Wallplate 1G Duplex W/Out Line Iv

Pass & Seymour/Legrand

Catalog Number	P8I
Manufacturer	Pass & Seymour/Legrand
Description	Plastic Plate, Single Gang, Duplex Without Line Is Molded Of Non-Combustible Mar-Proof Material. It Is Resistant to Discoloration, Grease, Oil, Solvent, and Moisture. The Seven Standard Colors Available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.
Weight per unit	0.0600 (lbs/each)
Product Category	Wall Plates & Covers

Features

cutout	Receptacle
indoor/outdoor	Indoor
insulation	Bare
media	Yes
Mounting Type	Strap Mounted
Number of Gangs	1
orientation	Vertical
Wall Plate Type	Duplex Receptacle

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	5"
Thickness	0.07

Descriptions

Construction	Plastic
Description	PLASTIC WALLPLATE 1G DUPLEX W/OUT LINE IV
extra long description	P&S SP8I PLATE PLASTIC 1G DUPLEX W/
Long Description	Plastic Plate, single gang, duplex without line is molded of non-combustible mar-proof material. It is resistant to discoloration, grease, oil, solvent, and moisture. The seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.
Product Type	Plate Plastic 1G Duplex W/Out Line I
Special Features	Non-combustible mar-proof material, seven standards colors, individually wrapped



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007680362
Manufacturers Part Number	SP8I
UPC	785007680362

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Wall Plate

Packaging

Carton	1
Package	25
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting standard	WALL CSA, UL, CSA, UL514