



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **PB24XS Encl 2H N4X SS4 PB** *Cooper B-Line/Cable Tray*

Catalog Number	PB24XS
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Push Button Enclosures, 5.75" Height, 3" Length, 3.25" Width, Nema 4X, Screw Cover, PB4XS Enclosure, Surface Mounted, Small Single Door, External Mounting Feet, 304 Stainless Steel, Oil-Resistant Gasket
Weight per unit	2.1 (lbs/each)
Product Category	Control Station Enclosures

### **Features**

dimensions	3.0000 IN X 3.2500 IN X 5.7500 IN
Material	304 Stainless Steel

### **Material, Color, and Finish**

Color	Gray
-------	------

### **Descriptions**

Description	ENCL 2H N4X SS4 PB
extra long description	B-LINE PB2-4XS TYPE 304 STAINLESS P
Features	Eaton's B-Line series push button enclosures provide reliable environmental protection and are designed to mount standard 30.5 mm or miniature 22.5 mm oil-tight pushbuttons, pilot lights and switches
Long Description	Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PB4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket
Product Type	Type 304 Stainless Pushbutton Enc
Special Features	Removable cover, recessed pull ring, s.s. screws

### **Manufacturer Information**

Brand	Eaton
GTIN	00782051136951
Manufacturers Part Number	PB2-4XS
UPC	782051136951

### **Taxonomies, Classifications, and Categories**

Category Description	STANDARD DUTY PUSHBUTTONS (10250H-)
Type	Push button enclosures

### **Packaging**

Carton	1
Weight Per each	2.052



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
nema rating	4X
standard	Not Applicable,Not Applicable