



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PB2M4XS Encl 5.75X3.25X3" N4X SS4 2H 22.5MM PB *Cooper B-Line/Cable Tray*

Catalog Number	PB2M4XS
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Push Button Enclosures, 5.75" Height, 3" Length, 3.25" Width, Nema 4X, Screw Cover, PBM4XS Enclosure, Surface Mounted, Small Single Door, External Mounting Feet, 304 Stainless Steel, Oil-Resistant Gasket
Weight per unit	2.1 (lbs/each)
Product Category	Control Station Enclosures

Features

dimensions	3.0000 IN X 3.2500 IN X 5.7500 IN
Material	304 Stainless Steel

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	ENCL 5.75X3.25X3" N4X SS4 2H 22.5MM PB
extra long description	B-LINE PB2M-4XS TYPE 12 STD PUSHBUT
Features	Eaton's B-Line series push button enclosures provide reliable environmental protection and are designed to mount standard 30.5 mm or miniature 22.5 mm oil-tight pushbuttons, pilot lights and switches
Long Description	Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket
Product Type	Type 12 STD Pushbutton Enc
Special Features	Removable cover, recessed pull ring, s.s. screws

Manufacturer Information

Brand	Eaton
GTIN	00782051138146
Manufacturers Part Number	PB2M-4XS
UPC	782051138146

Taxonomies, Classifications, and Categories

Type	Push button enclosures
------	------------------------

Packaging

Carton	1
Package	2
Weight Per each	2.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
nema rating	4X
standard	Not Applicable,Not Applicable