

Eaton PB2M-4XS

Catalog Number: PB2M-4XS

Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series push button enclosures	PB2M-4XS
	UPC
	782051138146
Product Length/Depth	Product Height
3 in	5.75 in
Product Width	Product Weight
3.25 in	2.1 lb
Compliances	Certifications
Not Applicable	Not Applicable



Material/finish

Material

304 stainless steel

Wall thickness

16 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Small single door

Model

PBM4XS enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

External mounting feet

Special features

Removable cover, recessed pull ring, s.s. screws

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - PB2M-4XS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton PB2M-4XS

Catalog Number: PB2M-4XS

Eaton B-Line series push button enclosures, 5.75" height, 3" length, 3.25" width, NEMA 4X, Screw cover, PBM4XS enclosure, Surface mounted, Small single door, External mounting feet, 304 stainless steel, Oil-resistant gasket

Photo is representative

General specifications

Product Name	Catalog Number
Eaton B-Line series push button enclosures	PB2M-4XS
	UPC
	782051138146
Product Length/Depth	Product Height
3 in	5.75 in
Product Width	Product Weight
3.25 in	2.1 lb
Compliances	Certifications
Not Applicable	Not Applicable



Material/finish

Material

304 stainless steel

Wall thickness

16 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Small single door

Model

PBM4XS enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

External mounting feet

Special features

Removable cover, recessed pull ring, s.s. screws

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Pushbutton-enclosure-operator.pdf](#)

Specifications and datasheets

[Eaton Specification Sheet - PB2M-4XS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)