



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PCMB2 Comb Numb&Letter Book *Panduit Corporation*

Catalog Number	PCMB2
Manufacturer	Panduit Corporation
Description	Stronghold PCMB-2 Pre-Printed Wire Marker Books Are Conveniently Pocket-Sized and Contain Wire Labels Printed On Vinyl Cloth. Markers Are Durable Enough For Up to 5 Years and Are Designed to Withstand Various Outdoor Environments. They Can Also Be Torn In Half to Label Each End Of The Conductor. Legend: A-Z, 1-15, +, -, /, 10 Markers Per Legend, and 10 Pages Per Book.
Weight per unit	1.0 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Legend	A thru Z, 0 thru 15, +, -, /
Material	Vinyl Cloth
media	Yes
Number of Markers	100
Wire Size	0.38

Dimensions and Weight

Diameter	0.38
Length	1.38
Size	0.22 x 1.56 es
Width	NA

Descriptions

Description	COMB NUMB&LETTER BOOK
extra long description	PAN PCMB-2 StrongHold™ PCMB-2 Pre-P
Long Description	StrongHold PCMB-2 Pre-Printed Wire Marker Books are conveniently pocket-sized and contain wire labels printed on vinyl cloth. Markers are durable enough for up to 5 years and are designed to withstand various outdoor environments. They can also be torn in half to label each end of the conductor. Legend: A-Z, 1-15, +, -, /, 10 markers per legend, and 10 pages per book.
Product Type	Stronghold™ PCMB-2 Pre-Printed Wire Marker Book, 2, Vinyl CL

Manufacturer Information

Brand	PANDUIT
GTIN	00074983948017
Manufacturers Part Number	PCM-B2
UPC	074983948017



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description WIRE LUBE, MARKERS, & TIES

Type Pre-Printed Wire Marker Book

Packaging

Carton 1

Package 10

Weight Per each 1

Uses, Certifications, and Standards

standard RoHS Compliant

Temperature Rating 170