



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PDG53M1200E5CM PDG5, 3P, 1200A, 65KA/480V, Pxr20alsig

Eaton Corp

Catalog Number	PDG53M1200E5CM
Manufacturer	Eaton Corp
Description	Eaton Power Defense Molded Case Circuit Breaker, Globally Rated, Frame 5, Three Pole, 1200A, 65KA/480V, PXR20 Arms Lsig W/ Cam Link and Relays, No Terminals (Metric Tapped Conductors)
Weight per unit	50.0 (lbs/each)
Product Category	20220418100417

Features

Current Rating	1200 A
frame	5
media	Yes
Poles	Three-pole
Trip Type	PXR 20 LSIG w/ARMS
Voltage Rating	600 VAC

Descriptions

Description	PDG5,3P,1200A,65KA/480V,PXR20ALSIG
extra long description	ETN PDG53M1200E5CM PDG5,3P,1200A,65
Features	The Power Defense molded case circuit breaker portfolio is globally rated in a small footprint for easy adaptability no matter the application or project requirement. A circuit breaker with communicating electronic trip units and the ability to generate the data to help you optimize your facilities' performance, and to help keep your employees, customers and end-users safe by reducing the risk of arcflash events.
Long Description	Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 5, Three Pole, 1200A, 65kA/480V, PXR20 ARMS LSIG w/ CAM Link and Relays, No Terminals (Metric Tapped Conductors)
Product Type	PDG5, 3P, 1200A, 65KA/480V, Pxr20alsig
Special Features	CAM / Relays

Manufacturer Information

Brand	Eaton
GTIN	00786679693209
Manufacturers Part Number	PDG53M1200E5CM
UPC	786679693209



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	50

Uses, Certifications, and Standards

standard	UL 489,CSA,CCC Marked,IEC 60947-2,RoHS Compliant
----------	--