



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PFME30LCYUNV3466 Indust-Pfme Led Flood 30000 Lumen 200-480 Vac *Crouse-Hinds*

| | |
|------------------|--|
| Catalog Number | PFME30LCYUNV3466 |
| Manufacturer | Crouse-Hinds |
| Description | Eaton Crouse-Hinds Series Pfme Led Floodlight, Cool White, Dimmable Driver, 750W-1000W Hid Equivalent, 50/60 HZ, Polycarbonate Lens, 30000 Lumens, 127 LM/W, Aluminum, Yoke Mount, Standard 120° Angle, > 0.90 PF, 277-480 Vac, 242W |
| Weight per unit | 77.0 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|------------|-------------------------------------|
| dimensions | 20.1600 IN X 4.1700 IN X 12.5000 IN |
|------------|-------------------------------------|

Descriptions

| | |
|------------------------|---|
| Description | INDUST-PFME LED FLOOD 30000 LUMEN 200-480 VAC |
| extra long description | CRS-H PFME30LCY-UNV34-66 PFME30LCY- |
| Features | PFME LED floodlights are certified for use wet locations and are UL Listed and CSA certified. These floodlights are suitable for locations requiring continuous and consistent light levels in extreme ambient temperatures and where wet, dusty, hot and/or cold conditions exist. |
| Long Description | Eaton Crouse-Hinds series PFME LED floodlight, Cool white, Dimmable driver, 750W-1000W HID equivalent, 50/60 Hz, Polycarbonate lens, 30000 lumens, 127 lm/W, Aluminum, Yoke mount, Standard 120° angle, > 0.90 PF, 277-480 Vac, 242W |
| Product Type | PFME30LCY-UNV34-66 |

Manufacturer Information

| | |
|---------------------------|--------------------|
| Brand | Eaton |
| GTIN | 00662276966833 |
| Manufacturers Part Number | PFME30LCY-UNV34-66 |
| UPC | 662276966833 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |
| Type | FLOODLIGHT |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 77 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Ind Facilities & Factories - Facility: Lighting and Lighting Controls |
|-------------|---|